


GENERAL INFORMATIONS

GENERAL INFORMATIONS	Battery name	IT5 AGM	
	Product Range	ITINERIS AGM - Stop & Start: Absorptive glass mat	
	European Type No. (ETN)	595.901.085	
	Polarity	DX	
	Technology	AGM	
	Application	Stop & Start	
	Standard ref.	EN 50342-1; EN 50342-2	

The new JET BATTERY that completes our line of products for Stop&Start motors with braking energy recovery. The AGM (Absorptive Glass Mat) battery's electrolyte is completely absorbed by the separator, so that the acid is retained even if the unit is overturned for a long period of time. Gas recombination technology and the use of caps with valves on each cell enable the battery to be installed in the passenger and luggage compartments. The design of the grilles and the composition of the active material makes it especially suited to cyclic applications.

Voltage (V)	12	Dimensional group	LN5
Capacity 20h (Ah)	95	Sizes (LxWxH) (mm)	353 x 175 x 190
Cold cranking Amps (CCA), EN (A)	850	Base Hold-Down	B3(f)
Energy at 20hrs rate and 25C (Wh)	1,135	Lay-out/Terminals	0 / 1
Cranking Power 10" at -18°C (KW)	6,6	Battery weight \pm 5% (kg)	26,4
Case	PP/PE	Colour	Black
Lid	PP/PE	Colour	Black
Plug	PP/PE	Colour	Black

GENERAL CHARACTERISTICS



+212 523 316 616 info@thejetbattery.com

+212 523 302 368 www.thejetbattery.com

BOX